



## Main

Range of Product	Harmony 9001K
Product or Component Type	Head for selector switch
Device short name	K
Type of operator	maintained
Operator profile	Without cap without knob

## Complementary

Bezel material	Metal
Mounting diameter	1.18 in (30 mm)
Operator position information	2 positions
Contacts type and composition	Without contact block
Device presentation	Basic element
Operator profile	Without handle
Type of operator	Stay put
Size	30 mm
Cam profile	5

## Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CSA LR24590 class 3211 03 CE UL listed file E42259 CCN NKCR

## Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	3389118039964
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.80 in (7.112 cm)
Package 1 Width	2.30 in (5.842 cm)
Package 1 Length	2.10 in (5.334 cm)
Package 1 Weight	4.32 oz (122.47 g)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------