


REVISIONS

A



B

B

A

SINGLE POLE	OFF-(ON) MOMENTARY	FLYING LEADS WITH HEAT SHRINK TUBE	FLAT, MATTE BLUE	BLUE	PB6B2FM7M1CAL07Y500	2-2329389-5
				GREEN	PB6B2FM7M1CAL06Y500	2-2329389-4
				YELLOW	PB6B2FM7M1CAL05Y500	2-2329389-3
				RED	PB6B2FM7M1CAL03Y500	2-2329389-2
				WHITE	PB6B2FM7M1CAL01Y500	2-2329389-1
			FLAT, MATTE GREEN	BLUE	PB6B2FM6M1CAL07Y500	2-2329389-0
				GREEN	PB6B2FM6M1CAL06Y500	1-2329389-9
				YELLOW	PB6B2FM6M1CAL05Y500	1-2329389-8
				RED	PB6B2FM6M1CAL03Y500	1-2329389-7
				WHITE	PB6B2FM6M1CAL01Y500	1-2329389-6
			FLAT, MATTE YELLOW	BLUE	PB6B2FM5M1CAL07Y500	1-2329389-5
				GREEN	PB6B2FM5M1CAL06Y500	1-2329389-4
				YELLOW	PB6B2FM5M1CAL05Y500	1-2329389-3
				RED	PB6B2FM5M1CAL03Y500	1-2329389-2
				WHITE	PB6B2FM5M1CAL01Y500	1-2329389-1
			FLAT, MATTE RED	BLUE	PB6B2FM3M1CAL07Y500	1-2329389-0
				GREEN	PB6B2FM3M1CAL06Y500	2329389-9
				YELLOW	PB6B2FM3M1CAL05Y500	2329389-8
				RED	PB6B2FM3M1CAL03Y500	2329389-7
				WHITE	PB6B2FM3M1CAL01Y500	2329389-6
			FLAT, MATTE BLACK	BLUE	PB6B2FM2M1CAL07Y500	2329389-5
				GREEN	PB6B2FM2M1CAL06Y500	2329389-4
				YELLOW	PB6B2FM2M1CAL05Y500	2329389-3
				RED	PB6B2FM2M1CAL03Y500	2329389-2
				WHITE	PB6B2FM2M1CAL01Y500	2329389-1
POLE	THROW	TERMINAL TYPE	CAP TYPE & COLOR	LED COLOR	TE DESCRIPTIVE PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm[INCHES]

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.4[.016]
2 PLC ±0.25[.010]
3 PLC ±
4 PLC ±
ANGLES ±5°
FINISH

-
-

DWN
RAVL.S
22FEB2018

CHK
ALEXANDER SHARPE
22FEB2018

APVD
ALEXANDER SHARPE
22FEB2018

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
SWITCH,PUSHBUTTON,FLAT CAP WITH LED,
FLYING LEADS WITH HEAT SHRINK,
SEALED, OFF-(ON)

SIZE
A200779

CAGE CODE
C-2329389

DRAWING NO

RESTRICTED TO

SCALE
3:1

SHEET
2 OF 2

REV
B

1471-9 (3/13)