

Han 32A-Protect. Cover-M-f. Hood+Base



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 032 5401
Specification	Han 32A-Protect. Cover-M-f. Hood+Base
HARTING eCatalogue	https://b2b.harting.com/09200325401

Identification

Category	Accessories
Series of hoods/housings	Han A [®]
Type of accessory	Protection cover
Description of the accessory	for hoods Metal

Version

Size	32 A
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Surface (hood/housing)	Powder-coated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	26 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140040267
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors