




- 1 CONTINUOUS STRIP ON REEL.
- 2 P/N 61760-2 IS REVERSE REELED.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

SECTION A-A
SCALE 10:1

SECTION B-B
SCALE 10:1

3 OBSOLETE	3.56 [.140] MAX DIA	20-16 AWG	2 61760-2 61760-1
	INSULATION RANGE	WIRE RANGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PHILLIP M FORTNEY 05OCT98	AMP AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK JEFF R RUTH 05OCT98		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
	0 PLC ±-		APVD DONALD DECKER 05OCT98	
	1 PLC ±-		PRODUCT SPEC	
	2 PLC ±0.25 [.010]		APPLICATION SPEC	
MATERIAL #4HD PHOS BRONZE		FINISH 0.003302[.000130] MAX PRE-TIN PLATE	WEIGHT -	SIZE A2
		CUSTOMER DRAWING		SCALE 6:1
		SHEET 1 OF 1		REV E1