


D




C

B

A



MATING FACE



THIS PRODUCT HAS NOT COMPLETED
VALIDATION TESTING

- 1

FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.
CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194
REAR GROMMET & INTERFACIAL SEAL: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1.
- 2

PART TO MARKED WITH TE IDENTIFICATION, TE PART NO.
AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.
3.

THIS INSERT CONTAINS: 16 CAVITIES FOR SIZE 20 PIN CONTACTS
6 CAVITIES FOR SIZE 16 PIN CONTACTS
4.

THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL SA.

NON-ENV	GPRBN22PB	1738151-3
GROMMET ONLY	GPRBH22PB	1738151-2
ENVIRONMENTAL	GPRBE22PB	1738151-1
REMARKS	DESCRIPTIVE PART NO.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C.C. THOMAS
CHK
K. HOGAN
APVD
K. HOGAN

10-8-10
10-8-10
10-8-10

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

MATERIAL

DWN
C.C. THOMAS
CHK
K. HOGAN
APVD
K. HOGAN

10-8-10
10-8-10
10-8-10

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
INSERT ASSEMBLY, PIN,
ARRANGEMENT 22, KEY B, GPRB
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-1738151

RESTRICTED TO
-

SCALE
4:1

SHEET
1

OF
1

REV
B

1471-9 (3/11)