










Max. Temperature: 260° during 10 seconds.

0955 169 3811 741	1	M3	Black insulator	Reel Packaging: 140 connectors (See details on page2/2)				
0955 169 3812 741	1	4-40 UNC						
0955 169 6811 741	2	M3						
0955 169 6812 741	2	4-40 UNC						
0955 169 7811 741	3	M3						
0955 169 7812 741	3	4-40 UNC						
Part number	PL	Nut	Index designation					
 All Dimensions in mm Original Size DIN A 3			Techn. Character.		Free size tolerances			
				Dat.	Name	Scale 2 : 1	D-Sub SMT, 9 poles Male, Straight with nuts and ground pins	
			Detail.	14-Sep-11	Johnson.S			
			Insp.	17-Nov-11	Steven.W			
			Stand.	17-Nov-11	Steven.W			
EC04070	17-Nov-11	Johnson.S	Zhuhai HARTING Limited					TB 09 55 169 x81x
Mod.	Dat.	Name	Sub.					



Detail A



See TB 09 55 169 x81x folio 1/2
for connector dimensions
and PCB layout

Packaging in accordance with
EIA 481-2.

0955 169 3811 741	1	M3	Black insulator	Reel Packaging: 140 connectors
0955 169 3812 741	1	4-40 UNC		
0955 169 6811 741	2	M3		
0955 169 6812 741	2	4-40 UNC		
0955 169 7811 741	3	M3		
0955 169 7812 741	3	4-40 UNC		
Part number	PL	Nut	Index designation	

All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances	
				Dat.	Name	Scale	D-Sub SMT, 9 poles Male, Straight with nuts and ground pins
			Detail.	14-Sep-11	Johnson.S		
			Insp.	17-Nov-11	Steven.W		
			Stand.	17-Nov-11	Steven.W		
EC04070	17-Nov-11	Johnson.S	Zhuhai HARTING Limited			TB 09 55 169 x81x	Page 2/2
Mod.	Dat.	Name				Sub.	