




P1



P2

DB9P FEMALE

NOTES:

- 1.ELECTRICAL TEST:100% OPEN,SHORT&MISSWIRE TEST.
- 2.CONDUCTOR RESISTANCE:2ohm,
INSULATOR RESISTANCE:10M ohm.
- 3.HIGH VOLTAGE:DC 300V 0.01sec.
- 4.MUST BE ROHS COMPLIANT.

BOM

4	SPONGE	36*31*4MM BLACK	1PCS
3	TERMINAL	KF141R-2.54-9P COLOR GREEN	1PCS
2	PCB	36*31*1.6MM PCB COLOR GREEN	1PCS
1	Connector	DB9 FEMALE PIN GOLD PLATED SHELL NICKEL PLATED PLASTIC:BLACK	1PCS
NO.	Name	SPECIFICATION	Q'TY

Premier Cable MFG Co Ltd

TITLE	DBP FEMALE ADAPTER				
	CUSTOMER		PCM-T-9F		
	CUSTOMER'S ITEM				
	SCALE	1:1	DRAWN BY	Steve	DATE 2020.02.12
UNIT	mm	CHECKED BY		DRAWING NO.	
REV.	A	APPROVED BY		PCM-USB-105	