



Pushing Performance  
Since 1945

# Han B Hood Side Entry 4 Pegs PG 21



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 09 30 016 0520                                                                        |
| Specification      | Han B Hood Side Entry 4 Pegs PG 21                                                    |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09300160520">https://b2b.harting.com/09300160520</a> |

## Identification

|                          |                   |
|--------------------------|-------------------|
| Category                 | Hoods/Housings    |
| Series of hoods/housings | Han® B            |
| Type of hood/housing     | Hood              |
| Type                     | High construction |

## Version

|                      |                                                   |
|----------------------|---------------------------------------------------|
| Size                 | 16 B                                              |
| Version              | Side entry                                        |
| Cable entry          | 1x Pg 21                                          |
| Locking type         | Double locking lever                              |
| Field of application | Standard hoods/housings for industrial connectors |

## Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65                                           |
|                                        | IP66                                           |
|                                        | IP67                                           |
| Type rating acc. to UL 50 / UL 50E     | 4                                              |
|                                        | 4X                                             |
|                                        | 12                                             |

## Material properties

|                         |                    |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
|-------------------------|--------------------|



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                            |
|--------------------------------------|----------------------------|
| Surface (hood/housing)               | Powder-coated              |
| Colour (hood/housing)                | RAL 7037 (dust grey)       |
| RoHS                                 | compliant                  |
| ELV status                           | compliant                  |
| China RoHS                           | e                          |
| REACH Annex XVII substances          | Not contained              |
| REACH ANNEX XIV substances           | Not contained              |
| REACH SVHC substances                | Not contained              |
| California Proposition 65 substances | Yes                        |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08)       |
| Requirement set with Hazard Levels   | R1 (HL 1-3)<br>R7 (HL 1-3) |

## Specifications and approvals

|           |                                                            |
|-----------|------------------------------------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE<br>DNV GL                                               |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 223 g                                    |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140045934                            |
| ETIM                           | EC000437                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |