


A


B

C

D



Ersatz für	Ausf.	Maß	
		a	b
Rel.stv. 73, T 23	C 50	17	8
Rel.stv. 73, T 4	C 51 ¹⁾	19,5	8
Rel.stv. 73, T 24	C 52	23	10



√ R_t 16

Hierzu paßt C42 334 - A 100 - C55...C57
 1) Vorzugstypen - A 100 - B10...B12
 Obfl. 648 / 865

					Freimaßtoleranzen		Rd DIN 1756 - CuZn 39 Pb 3 Zh 6	
					js 14; JS14 ±1°			
					Bearb.	Tag	Name	Stift
					Gepr.	30.1.68	J. Schaberg	
					Norm.	22.5.68	2. Be	
03	WB 87/016	30.10.86	HB					Maßstab 5:1 1:1
2	69C42A412	17.2.69	HB					
1	68C42A504	24.5.68	HB					
51	—	—	—		SIEMENS AG		C42 334 - A 100 - C50...C52	- *6
Ausgabe	Änderung	Tag	Name				Ersatz für Rel. stv. 73, T4, T23, T24	