



Pushing Performance
Since 1945

Han-Yellock 60M-hood-M32 side entry



Image is for illustration purposes only. Please refer to product description.

Part number	11 13 600 1502
Specification	Han-Yellock 60M-hood-M32 side entry
HARTING eCatalogue	https://b2b.harting.com/11136001502

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Shell

Version

Size	Han-Yellock® 60
Version	Side entry
Cable entry	1x M32
Locking type	Push button
Field of application	Hoods/housings for outdoor applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7021 (black grey)
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	165 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140110601
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors