



THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		B1	REVISED ECR-07-028230	26NOV07	A,L	S,Y



SECT B-B



SECT A-A





NOTES:



- ① USE WITH: MT REC CONN P/N: X-353293-X
CRIMP HSG P/N: X-353908-X
CRIMP CONT P/N: 353907-1
353918-1(L/P)
- ② USE WITH POWER CONTACT P/N: 1123907-1 (NOT ASSEMBLED WHEN SHIPPED)
- ③ MATERIAL:
HOUSING: GLASS FILLED THERMOPLASTIC, UL94V-0, GRAY
SIGNAL CONTACT: BRASS
- ④ FINISH (SIGNAL CONTACT):
NICKEL UNDERPLATE ALL OVER
LATTICE MATING AREA: GOLD PLATE
MINI CT MATING AREA: MATTE TIN PLATE
- ⑤ LOCATION OF DATE CODE: AABBCD(N)
(AA: YEAR, BB: WEEK, C: DAY OF WEEK, D: DAYTIME, N: NIGHT)

11.3	25.82	3.75	4.25	34.7	33.7	45.7	53.7	C	14(6+8)	4	5-292246-4
11.3	25.82	3.75	4.25	34.7	33.7	45.7	53.7	B	14(6+8)	4	3-292246-4
11.3	25.82	2.05	2.55	34.7	33.7	45.7	53.7	A	14(6+8)	4	1-292246-4
WEIGHT (g)	G	F	E	D	C	B	A	KEY TYPE	SIGNAL	POWER	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN J. JIANG 05FEB03	Tyco Electronics Corporation Shanghai, PRC 200233	
DIMENSIONS: mm				CHK S.Y 05FEB03		
				APVD T. SASAKI 05FEB03	NAME	
				PRODUCT SPEC 108-60028	RECEPTACLE ASSEMBLY FOR AMP 1.5 PITCH MINI CT HYBRID LATTICE CONNECTOR	
MATERIAL SEE NOTE				APPLICATION SPEC 114-5256	SIZE A2	CAGE CODE 00779
FINISH SEE NOTE				WEIGHT	DRAWING NO C-292246	RESTRICTED TO
CUSTOMER DRAWING				SCALE NTS	SHEET 1 of 3	REV B1



SECT B-B



SECT A-A



- NOTES:
- ① USE WITH MT REC CONN P/N: X-353293-X
CRIMP HSG P/N: X-353908-X
CRIMP CONT P/N: 353907-1
353918-1(L/P)
 - ② USE WITH POWER CONTACT P/N: 1123907-1 (NOT ASSEMBLED WHEN SHIPPED)
 - ③ MATERIAL:
HOUSING: GLASS FILLED THERMOPLASTIC, UL94V-0, GRAY
SIGNAL CONTACT: BRASS
 - ④ FINISH (SIGNAL CONTACT):
NICKEL UNDERPLATE ALL OVER
LATTICE MATING AREA: GOLD PLATE
MINI CT MATING AREA: MATTE TIN PLATE
 - ⑤ LOCATION OF DATE CODE: AABBCD(N)
(AA: YEAR, BB: WEEK, C: DAY OF WEEK, D: DAYTIME, N: NIGHT)

13.0	31.82	6.75	7.25	40.7	39.7	51.7	59.7	C	22(10+12)	4	6-292246-2
13.0	31.82	6.75	7.25	40.7	39.7	51.7	59.7	B	22(10+12)	4	4-292246-2
13.0	31.82	5.05	5.55	40.7	39.7	51.7	59.7	A	22(10+12)	4	2-292246-2
WEIGHT (g)	G	F	E	D	C	B	A	KEY TYPE	SIGNAL	POWER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	±

DWN —

CHK —

APVD —

PRODUCT SPEC —

APPLICATION SPEC —

WEIGHT —

CUSTOMER DRAWING

Tyco Electronics Corporation
Shanghai ,PRC 200233

NAME

RECEPTACLE ASSEMBLY
FOR AMP 1.5 PITCH MINI CT
HYBRID LATTICE CONNECTOR

SIZE A2

CAGE CODE 00779

DRAWING NO C=292246


RESTRICTED TO —

SCALE NTS

SHEET 2 OF 3

REV B1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
—	—	—	—	SEE SHEET 1	—	—



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH		

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Shanghai ,PRC 200233

NAME

RECEPTACLE ASSEMBLY
FOR AMP 1.5 PITCH MINI CT
HYBRID LATTICE CONNECTOR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=292246

—

SCALE

NTS

SHEET

3 OF 3

REV

B1