

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2016


© COPYRIGHT 2003

BY TE Connectivity





ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISED (ECR-16-004121)	21.MAR.'16	JM	JW
	D3	REVISED (ECR-16-009804)	07JUL2016	JM	JW
	D4	REVISED (ECR-17-000376)	10JAN2017	JM	JW
	D5	REVISED (ECR-17-014365)	28SEP2017	HH	YJ



IN CLOSED POSITION



NOTE

1. BE MATED WITH HEADER HSG (P/N : 936287) SMOOTHLY
2. CODE IS AS FOLLOWS: SEE TABLE 1.
3. APPLICABLE RECEPTACLE CONTACT P/N

PART NO.	DESCRIPTION	WIRE SIZE(mm ²)
928999-1	MQS RECEPTACLE TML (SOCKET CONTACT)	0.2 ~ 0.5
963715-1	MQS RECEPTACLE TML (SOCKET CONTACT)	0.75

- MQS CONTACT(AVX: 0.5mm² / AVSS-X: 0.75mm²)
- LOCKING FORCE : MIN 4kgf (FORCE WITH FULL PINS APPLIED, ONLY EXPORT)
- LOCKING FORCE : OVER 8kgf
- 6. GENERAL TOLERANCE

GENERAL TOLERANCES	
10 MAX	±0.3
10 OVER 30 MAX	±0.2
30 OVER 100 MAX	±0.25
ANGLES	±3°

D5

(TABLE 1) SCALE 2:1

CODE A : TBD	CODE B : TBD	CODE C : 3-936289-4
CODE D : TBD	CODE E : 936289-7, 936289-5, 936289-3, 936289-2	

NO.	CODE	COLOR	MATERIAL	DESCRIPTION	PART NO.
D4	E	GRAY	PA66	SOCKET HSG 6P	5 936289-3
	E	BLACK	PA66	SOCKET HSG 6P	5 936289-2
	E	NATURAL	PBT	SOCKET HSG 6P	4 936289-5
	E	GREEN	PA66	SOCKET HSG 6P	5 936289-7
	D	-	PBT	SOCKET HSG 6P	TBD
	C	BROWN	PA66	SOCKET HSG 6P	5 3-936289-4
	B	-	PBT	SOCKET HSG 6P	TBD
	A	-	PBT	SOCKET HSG 6P	TBD

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±
MATERIAL	FINISH -
SEE TABLE	

DWN JM JEON

CHK -

APVD JW JUNG

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME MQS. SOCKET HOUSING 6POS

SIZE A3 CAGE CODE 00779 DRAWING NO C-936289 RESTRICTED TO -

SCALE 3:1 SHEET 1 OF 1 REV D5