

Fixing spanner for hexagon nut**5.58.002.034/0000****General information**

Fitting for	RAFIX 16
-------------	----------

Other specifications

Shock resistance acc. to IEC 60068-2-27	amplitude < 50g, 11ms, half sinusoidal
---	--

Ambient temp. operating min.	-25 °C
------------------------------	--------

Ambient temp. operating max. with lamp /LED	+55 °C
---	--------

Storage temperature min.	-40 °C
--------------------------	--------

Storage temperature max.	+85 °C
--------------------------	--------

Environmental resistance	acc. to IEC 60068-2-14, -30, -33 and -78
--------------------------	--

Hot wire ignition acc. to IEC 60695-2-1	yes
---	-----

Resistance to vibrations acc. to IEC 60068-2-6	10 g at 20 ... 500 Hz
--	-----------------------

ROHS compliant	yes
----------------	-----

REACH compliant	yes
-----------------	-----