

LOC		DIST		REVISIONS			
ES	00	F	LYR	DESCRIPTION	DATE	DWN	APVD
		A		REV PER ECR-08-018624	25JUL2008	CZ	SY

D

C

B


A

D




C

B

A




- ① "AMP", PART NUMBER, AND DATE CODE TO BE MARKED IN AREA SHOWN
- ② MATERIAL: HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC, UL94 V-0
SIGNAL CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- ③ CONTACT PLATING: SIGNAL CONTACTS - .000050 MIN Ni UNDER ALL
.000030 MIN Au ON CONTACT AREA
.000100 MIN Sn AT PCB INTERFACE
POWER CONTACTS - .000050 MIN Ni UNDER ALL
.000030 MIN Au ON CONTACT AREA
.000100 MIN Sn AT PCB INTERFACE
- ④ MECHANICAL CONNECTOR KEEP OUT ZONE
- ⑤ DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- ⑥ PCB - ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES
- ⑦ PCB - .0453±.0010 DRILLED HOLES PLATED WITH .0003 MIN Sn OVER
.001 TO .003 CU PLATING TO ACHIEVE A .040 DIA HOLE



SECTION Y-Y

12S + 11P	1888120-2
DESCRIPTION	PART NUMBER

DWN C. ZHOU 29FEB2008		DWN S. ZHAO 29FEB2008		Tyco Electronics Tyco Electronics incorporation Shanghai, P.R.China.200233	
CHK S. YAO		APVD S. YAO		NAME	
PRODUCT SPEC		108-1973		APPLICATION SPEC	
114-13038		114-13038		SIZE CAGE CODE DRAWING NO	
WEIGHT		A100779C=1888120-2		RESTRICTED TO	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 2	
				REV A	

-NO CONTACTS LOADEDAMP 4805 REV 31MAR2000