




C.A.D. FILE CODE
S.C344085.D

DO NOT SCALE

DIMENSIONS IN MM.




344085-1



SAME POLARISATION BUT
DIFFERENT INHIBITIONS
(SEE "INHIB. VIEWS.")


VARIOUS POLARISATIONS FOR
1-344085-1 TO 1-344085-9 ONLY.

FOR REFERENCE ONLY
WILL NOT BE UP-DATED




(SHOWS A TYPICAL POLARISED A/BACKOUT)

7 SLOTS (AS SHOWN)



1-344085-9 (PINK)
INHIB. VIEW

7 SLOTS (AS SHOWN)



1-344085-8 (RED)
INHIB. VIEW

FOR REFERENCE ONLY
WILL NOT BE UP-DATED

OBSOLETE	PINK (RAL TBA)	NYLON 6.6	1-344085-9
OBSOLETE	RED (RAL3000)	NYLON 6.6	1-344085-8
OBSOLETE	BROWN (RAL8011)	NYLON 6.6	1-344085-7
OBSOLETE	GREY (RAL TBA)	NYLON 6.6	1-344085-6
OBSOLETE	BLACK (RAL9004)	NYLON 6.6	1-344085-5
OBSOLETE	VIOLET (RAL4005)	NYLON 6.6	1-344085-4
OBSOLETE	GREEN (RAL6001)	NYLON 6.6	1-344085-3
OBSOLETE	BLUE (RAL5015)	NYLON 6.6	1-344085-2
OBSOLETE	YELLOW (RAL1018)	NYLON 6.6	1-344085-1
	WHITE (RAL9002)	NYLON 6.6	344085-1
FINISH		MATERIAL	PART NUMBER
CUSTOMER DWG FOR REFERENCE ONLY		©COPYRIGHT 1987 BY AMP OF GREAT BRITAIN LTD. ALL INTERNATIONAL RIGHTS RESERVED. ALL PRODUCTS MAY BE COVERED BY BRITISH AND FOREIGN PATENTS AND/OR PATENTS PENDING.	RELEASED FOR PUBLICATION 12.6.87
D1	UPDATED	ECR-15-002885	11MAR2015
D	UPDATED	EB00-0277-93	21.7.93
C	ADDED CON.DIM.	C5375	28.9.88
B	REVISED	C5331	4/9/89
A	UPDATED	C4956	14.7.88
O	REL. FOR PROD.	C4891	9.3.88
REV	MODIFICATION	ECN	DATE
TOLERANCES UNLESS OTHERWISE STATED DEC ± 0.5 ANGLES ± 1°		DR. R.J.S.	12.6.87
NAME		CH. D.B.K.-M.	APP. B.J.
A/BACKOUT FOR 8 WAY REC. HSG. ECONOSEAL 3 HIGH CURRENT		AMP of Great Britain Ltd.	TERMINAL HOUSE STANMORE MIDDX.
SCALE	LOC	SIZE	DWG.No.
4/1	E	A2	C344085
REV	D1	SHEET	1/1