

Han-Eco 16B-Cover w. bearing bracket



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 016 5410
Specification	Han-Eco 16B-Cover w. bearing bracket

Identification

Category	Accessories
Series of hoods/housings	Han-Eco® B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings

Version

Size	16 B
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 Fire protection on railway vehicles

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85389099
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors