

Han 3M-HAE-M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 37 003 1645
Specification	Han 3M-HAE-M25
HARTING eCatalogue	https://b2b.harting.com/19370031645

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® M
Type of hood/housing	Hood

Version

Size	3 A
Version	Side entry
Cable entry	1x M25
Locking type	Single locking lever
Field of application	Hoods/housings for rough environments
Pack contents	With seal screw

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44
	IP65 With seal screw
	IP67 With seal screw

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

Specifications and approvals

Approvals	CE
	DNV GL

Commercial data

Packaging size	10
Net weight	80.5 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140170940
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors