

9001KS52K5

Key selector switch head, Harmony 9001K, metal, key switch, 30mm, key E10, 3 positions, return both sides to center



Main

Range of Product	Harmony 9001K
Product or Component Type	Head for key selector switch
Device short name	K
Type of operator	Spring return
Operator profile	Black key operated knob

Complementary

Bezel material	Metal
Mounting diameter	1.18 in (30 mm)
Operator position information	3 positions
Key number	E10
Key withdrawal position	Center
Contacts type and composition	Without contact block
Device presentation	Basic element
Operator profile	Key switch
Type of operator	Spring return
Size	30 mm
Return	Both sides to centre
Cam profile	2

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901913917
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.69 in (4.3 cm)
Package 1 Width	2.20 in (5.6 cm)
Package 1 Length	3.70 in (9.4 cm)
Package 1 Weight	6.88 oz (195.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------