

Coaxial Cable Connector 11_BNC-75-7-5/133_N

Description

Straight cable plug

Interface standards

Interface compatible with IEC 61169-8



Technical Data

Electrical Data

Impedance	75 Ω
Interface frequency max.	1 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0195 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPALATE (R) Plating
Body	Brass	SUCOPALATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPALATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPALATE (R) Plating

Related Documents

Catalogue drawing	DOU-00007315
Assembly instruction	DOC-0000178746

Ordering Information

Single package	11_BNC-75-7-5/133_NE
----------------	----------------------

Additional Information

Suitable cables	RG_11_A/U
-----------------	-----------