

**MULTIMODE DUPLEX ADAPTOR – ZIRCONIA SLEEVE
ALIGNEMENT**



 Series
SC

 Packaging
1

 Issue
04-01-2011

 Page
1/1

Original dimensions in mm [inch]


GENERAL

Type : IEC 60874-19 SC type. Push pull latching system
 Body color : beige

Mounting : snap-in (or screw –in) mounting max. Panel thickness 1.6mm

Alignment sleeve : Zirconia

CHARACTERISTICS (Dependant on fiber or cable construction)

Material : Plastic moulded Material in accordance with BELLCORE
 GR 326 CORE Issue 2, par.3.3.1
 Inflammability V1 (UL94)
 Stainless stell

Clip

Optical : Attenuation (according to IEC 61300-3-4:Substitution method, 7 type) at 1310nm :
 0.02 dB Max / 0.01 dB Typ

Mechanical : Durability Bellcore 326, 500 cycles
Plug Retention > 68 N

Environmental : Temperature range (storage/operating) -40°C to +85°C

Salt spray : EIA/TIA -455-16A, 35°C, 168 hr.

Vibration test : Bellcore 326, 10 to 50 Hz, 2 hrs./axis

Proof test : Bellcore 326, Straight pull : 6.8 Kg load at 0°
 Side pull : 3.5 Kg load at 90°

CREATION					
PEN/EP CAT					RADIALL [®]
Name: CAUSSE.C					101, rue P. Hoffmann
Date: 23 Jul.99					93116 ROSNY/BOIS
Appr.: LV					FRANCE
	4 jan 11	Mise à jour performances mécaniques	Poret	HD	Tel : (33) 0149353535
	10/01/02	Performance specified	Valencia	LV	Fax : (33) 0148546363
	Issue	Revisions	Name	Appr.	