


## DFN-10 to DIP-14 SMT Adapter (0.8 mm pitch, 4.0 x 4.0 mm body)

| REF. | DIMENSIONS |      |      |        |       |      |
|------|------------|------|------|--------|-------|------|
|      | mm         |      |      | inches |       |      |
|      | MIN.       | TYP. | MAX. | MIN.   | TYP.  | MAX. |
| A    |            | 3.20 |      |        |       |      |
| B    |            | 0.60 |      |        |       |      |
| C    |            | 0.30 |      |        |       |      |
| B2   |            | 2.60 |      |        |       |      |
| C2   |            | 3.00 |      |        |       |      |
| D    |            | 0.50 |      |        |       |      |
| D2   |            | 0.30 |      |        |       |      |
| E    |            | 0.80 |      |        |       |      |
| F    |            |      |      |        | 0.600 |      |
| G    |            |      |      |        | 0.100 |      |
| H    |            |      |      |        | 0.025 |      |

Top View (SMT Footprint)



(Representative drawing only - not to scale)

### Bottom View (DIP Pins)



(Representative drawing only - not to scale)

### Side View (DIP Pins)



(Representative drawing only - not to scale)