

Coaxial Cable Connector 24_BNC-50-4-10/133_N

Description

Straight bulkhead cable jack

Interface standards

IEC 61169-8_MIL-STD-348A/301_CECC 22120

Technical Data

Electrical Data

| | |
|--------------------------|-------------|
| Impedance | 50 Ω |
| Interface frequency max. | 4 GHz |
| Frequency range | DC to 2 GHz |
| Return loss | 38 dB |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | crimped |
| Outer contact | crimped |
| Weight | 0.0181 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|--------------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Brass | SUCOPALATE (R) Plating |
| Body | Brass | SUCOPALATE (R) Plating |
| Insulator | PTFE (Polytetrafluoroethylene) | |
| Gasket | VMQ (Silicone rubber) | |
| Fastening nut | Brass | SUCOPALATE (R) Plating |
| Washer | Bronze | SUCOPALATE (R) Plating |
| Crimp ferrule | Copper | SUCOPALATE (R) Plating |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00301696 |
| Assembly instruction | DOC-0000719520 |
| Mounting hole | DOU-00008751 |

Ordering Information

| | |
|----------------------|-----------------------|
| Bulk 100 pcs package | 24_BNC-50-4-10/133_NH |
| Single package | 24_BNC-50-4-10/133_NE |

Additional Information

| | |
|-----------------|---|
| Suitable cables | SPUMA_240, SPUMA_240-FR-01, Spuma_240-RS-FR |
|-----------------|---|