


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO-17-004099	29AUG2017	RS	DR
	D	REVISED PER ECO-18-001491	31JAN2018	RS	DR

 E13288 Listed	 LR7189 Certified
250-300 MCM STRANDED ONLY	250-300 MCM SOLID OR STRANDED



1 BODY MATERIAL THICKNESS $3.200 \pm 0.076 [1.126 \pm .003]$

2 STAMP AMP 250-300 MCM* APPROX AS SHOWN

25	LOOSE PIECE	323034
QTY	PACKAGE TYPE	PART NUMBER

DIMENSIONS: mm [INCHES]	DWN DK SCHRUM	6/12/92	MATERIAL COPPER ASTM B-152	FINISH .000100 MIN EXT THK TIN PLATE PER ASTM B545	 TE Connectivity Ltd.
	CHK RD HEIM	6/26/92			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD AJ KAUFMAN	6/26/92	NAME TERMINAL, RING TONGUE, SOLISTRAND, TM WIRE SIZE: 127.0-152.0mm ² [250-300] MCM	SIZE A4	CAGE CODE 00779
	PRODUCT SPEC UL 486 A-B				
0 PLC ± -	APPLICATION SPEC —		DRAWING NO C-323034	RESTRICTED TO —	SCALE 1:1
1 PLC ± -	WEIGHT				
2 PLC ± -	CUSTOMER DRAWING		SHEET 1 OF 1	REV D	
3 PLC ± 0.127[.005]					
4 PLC ± -					
ANGLES ± -					