

## HPP V4 EI-PFT metal housing with clip



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 595 0031
Specification	HPP V4 EI-PFT metal housing with clip
HARTING eCatalogue	<a href="https://b2b.harting.com/09455950031">https://b2b.harting.com/09455950031</a>

### Identification

Category	Connectors
Series	HARTING PushPull (V4)
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Easy Install With board locks With integrated seal

### Version

Locking type	PushPull
--------------	----------

### Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

California Proposition 65 substances	Lead
	Nickel

## Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	10
Net weight	22.8 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140061736
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors