

PLUG: WBB50PMT
RECEPTACLE: WB50SD6
XXXXXXXXXXXXX

PLUG
RECEPTACLE

SERIES

WBB 2 row, SMT, plug, with mounting ears
WBA 2 row, SMT, plug, full skirt, with mounting ears

WB 2 row, straight, receptacle, with mounting ears

SIZE

20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 128, 132

20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 128, 132

CONTACTS

TYPE CONTACTS/TERMINATIONS:

PMT Pin, card edge SMT (Board: .054/.070)

TYPE CONTACTS/TERMINATIONS:

SD6 Socket, straight, dip solder, .095"
SD9 Socket, straight, dip solder, .140"
SD12 Socket, straight, dip solder, .190"
SD19 Socket, straight, dip solder, .300"

HARDWARE

STYLE OF HARDWARE: (See WB-9)

K*_* Integral keying guides, polarized
KY*_* Stainless steel keying guides, polarized
JMM 2 stainless steel fixed jackscrews

STYLE OF HARDWARE: (See WB-9)

K*_* Integral keying guides, polarized
KY*_* Stainless steel keying guides, polarized
JTFF 2 stainless steel turning jackscrews

DIMENSIONS					
SIZE	A	B	C	D	E
20	1.150	.900	.450	1.030	.750
30	1.400	1.150	.700	1.280	1.000
40	1.650	1.400	.950	1.530	1.250
50	1.900	1.650	1.200	1.780	1.500
60	2.150	1.900	1.450	2.030	1.750
70	2.400	2.150	1.700	2.280	2.000
80	2.650	2.400	1.950	2.530	2.250
90	2.900	2.650	2.200	2.780	2.500
100	3.150	2.900	2.450	3.030	2.750
110	3.400	3.150	2.700	3.280	3.000
128	3.850	3.600	3.150	3.730	3.450
132	3.950	3.700	3.250	3.830	3.550