



Pushing Performance
Since 1945

DSUB MA STR HIGH VOLTAGE CONTACT



Image is for illustration purposes only. Please refer to product description.

Part number	09 69 281 2550
Specification	DSUB MA STR HIGH VOLTAGE CONTACT
HARTING eCatalogue	https://b2b.harting.com/09692812550

Identification

Category	Contacts
Series	D-Sub
Identification	Mixed
Type of contact	Solder contact
Description of the contact	Straight

Version

Termination method	Solder termination
Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.25 ... 0.5 mm ²
Conductor cross-section	AWG 24 ... AWG 20
Rated current	≤10 A
Rated voltage	3,000 V
Contact resistance	≤3 mΩ
Stripping length	1.5 mm
Limiting temperature	-55 ... +125 °C
Insertion force	≤5 N
Withdrawal force	≈2.5 N
Performance level	AU 50
	1



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥500
Test voltage $U_{r.m.s.}$	4 kV @ 50 Hz

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni
Layer thickness	≥1.27 µm
Layer thickness	≥50 µinch
Material (hood/housing)	Polycarbonate / Teflon (PTFE)
Material (locking)	PI
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	20
Net weight	0.6 g
Country of origin	Czechia
European customs tariff number	85366990
GTIN	5713140098916
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors