

DELTA PARTS NUMBERING SYSTEM

MODELS OTHER THAN POWER ENTRY MODULE TYPES AND P.C. BOARD MOUNTING TYPES

<u>03</u>	<u>GE</u>	<u>E</u>	<u>G3</u>	<u>V</u>	<u>-R</u>
					Option resistor
					Design sequence: (for cylinder types, the 8th digit designates the outside diameter; S- $\varnothing$ 38mm; M- $\varnothing$ 43mm; L- $\varnothing$ 50mm)
					Input/Output connection: G = lugs; W = PVC wires; S = screws G5 = 5 lugs (6.3*0.8mm) W5 = 5 wires (UL 1015 AWG#18, 4" long)
					Case style: A- Small mounting ears 90 degrees from terminal sides B- Triangle mounting ears 90 degrees from terminal sides C- Triangle mounting ears on terminal sides D- IEC connector with mounting screws E- IEC connector package F- Cylinder types G- Two-hole mounting bars, 90 degrees from terminal sides N- IEC connector with snap-in type
					Series: Electrical circuit, see specific catalog pages
					Current rating: AC rms e.g.: 03 amp

POWER ENTRY MODULE TYPES

<u>06</u>	<u>AR</u>	<u>2</u>	<u>D</u>
			Special design: A- with ground choke D- with double pole power switch for models AB, AK, AR series
			Module construction: 1- IEC connector & fuse holder 2- IEC connector, fuse holder and power switch 3- IEC connector, fuse holder, power switch and voltage selector switch 4- IEC connector, fuse holder & voltage selector switch 5- For models other than CK, CR series; same construction as 4 but with voltage selector switch at front panel
			Series: Electric circuit, see specific catalog pages
			Current rating: AC rms e.g.: 06 amp

PCB MOUNTING TYPES

<u>03</u>	<u>ME</u>	<u>3</u>	<u>A</u>	<u>-R</u>
				Option resistor
				Special design: A: with ground choke
				Design sequence
				Series: Electrical circuit, see specific catalog page
				Current rating: AC rms e.g. :03 amp

DELTA PARTS NUMBERING SYSTEM

3-Phase Types

10

TD

S6

D

Special Design:
Dual: diff. and common choke

Input/Output connection :

G = lugs; W = PVC wires; S = screws; T = terminal blocks
e.g.
G6 = 6 lugs
W6 = 6 wires
T2: 2 terminal blocks
TIW4: 1 terminal block / 4 wires

Series:

TD: used in "△" system
TDH: used in "△" system
TDR: used in "△" system, vertical style
TDV: used in "△" system, vertical style
TDS: used in "△" system, screw style
TY: used in both "△" & "y" system
TYS: used in "△" & "y" system, screw style
TYT: used in "△" & "y" system terminal block style
PT: P.C.B. Filter
PY: P.C.B. Filter

Current rating: AC rms
e.g.: 10 amp

