



DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19 .
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.


LOC		DIST		REVISIONS									
BD	39	P	F	ZONE	LTR	DESCRIPTION				DATE	APPROVED		
			✓		A	REVISED & REDRAWN ECN-1465				8-12-86	-		




1. GATES ARE SHIPPED ATTACHED TO RUNNER.

SIZE & GATE IDENTIFICATION LETTER
MOLDED IN AREA INDICATED

VIEW F-F



VIEW G-G



VIEW H-H

AS SHOWN	207468-1
REMARKS	PART NUMBER

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON :
2 PL DEC ± -
3 PL DEC ± .005
ANGLES ± -

MATERIAL
POLYPROPYLENE
COLOR: BLACK

FINISH

DR *S. Weldon 9/16/86*
CHK *C. Richard 9/16/86*
APPD *J. Schupf 9/16/86*
APPD *U. Kumar 9/16/86*
PRODUCT SPEC
APPLICATION SPEC
WEIGHT

AMP AMP INCORPORATED
Harrisburg, Pa. 17105

NAME

CABLE GATES, FOR SIZE 1, 90° & 180°
EXIT, AMPLIMITE®

SIZE	FSCH NO	DRAWING NO
C	00779	207468
SCALE	NTS	SHEET 1 OF 1

1-C	.160
1-B	.140
1-A	
GATE	CABLE DIA REF

AMP 1471-7 REV 10-84

CUSTOMER DRAWING