

9001KS88K14

Key selector switch head, Harmony 9001K, metal, key switch, 30mm, key E10, 4 positions, stay put



Main

Product or Component Type	Head for key selector switch
Enclosure type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Range of Product	Harmony 9001K

Complementary

Bezel material	Metal
Cap/operator or lens colour	black
Contacts type and composition	Without contact block
Key number	E10
Key withdrawal position	In any position
Operator position information	4 positions
Operator profile	Key switch
Operator profile	1 projecting push-button
Size	30 mm
Type of operator	Maintained
Type of operator	Stay put
Contacts type and composition	Without contact block

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	3389118039346
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	2.20 in (5.588 cm)
Package 1 Length	3.60 in (9.144 cm)
Package 1 Weight	6.56 oz (185.973 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------