

Han M Hood Angled Entry 2 Pegs PG 11



Image is for illustration purposes only. Please refer to product description.

Part number	09 37 003 1640
Specification	Han M Hood Angled Entry 2 Pegs PG 11
HARTING eCatalogue	https://b2b.harting.com/09370031640

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M
Type of hood/housing	Hood

Version

Size	3 A
Version	Side entry
Cable entry	1x Pg 11
Locking type	Single locking lever
Field of application	Hoods/housings for rough environments
Pack contents	With seal screw

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44
	IP65 With seal screw
	IP67 With seal screw

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

Specifications and approvals

Approvals	CE
	DNV GL

Commercial data

Packaging size	10
Net weight	82 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140055247
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors