





RoHs

General tolerances(mm)

0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500	0.1/10
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	±2'



Product model	PIN	A	B	C
DA381-141C1-2PG213	2	3.81	8.41	3.81
DA381-141C1-3PG213	3	7.62	12.22	7.62
DA381-141C1-4PG213	4	11.43	16.03	11.43
DA381-141C1-5PG213	5	15.24	19.84	15.24
DA381-141C1-6PG213	6	19.05	23.65	19.05
DA381-141C1-7PG213	7	22.86	27.46	22.86
.....				
DA381-141C1-24PG213	24	3.81x(N-1)	3.81xN+0.79	3.81x(N-1)

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/8	/	300/8
IEC Standard			
Overvoltage Category/Pollution Degree	II / 2		
Rated Voltage(V)/Current(A)	250/7		
Rate Impulse Voltage(KV)	2.5		
Pitch(mm)/Poles	3.81/N=02~24P		
Operating temperature(°C)	-40~+105		
Conform to RoHS	Yes		

2	Pin	Copper alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

GENERAL TOLERANCES
UNLESS SPECIFIED

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO. DA381-141C1-NPG213		TITLE: Socket-type terminal	
DESIGN: James	CUSTOMER	SIZE	UNITS
		A4	MM
CHED: Talen		SCALE	SHEET
APPD: Sophia		N:A	1/1