



CSTSB4U**CSTSB5U****Dimensions & Weight**

	CSTSB4U	CSTSB5U
Width	17 mm	17 mm
Length	50 mm	50 mm
Height w DIN Rail	35 x 7.5 mm 35 x 15 mm	40.7 mm 48.0 mm
Weight per piece	24 g	25.5 g

Technical Data/Ratings

Approvals		
Wire Size (solid / stranded)	22-6 AWG 1.5-10 mm ²	22-4 AWG 1.5-16 mm ²
Voltage Rating	600 V 1000V AC/DC	600 V 1000V AC/DC
Current Rating	65 A 57 A	80 A 76 A
Torque	14 lb-in 1.2 Nm	25 lb-in 2.0 Nm
Insulation Material	Polyamide 66	Polyamide 66

Installation Instructions

Wire Stripping Length	—	—
Screw / Stud Size	M4	M5
Screwdriver	Flat Head 1.0 x 5.5 mm	Flat Head 1.0 x 5.5 mm

Terminal Blocks

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
Grey (standard)	CSTSB4U	100	CSTSB5U	100
Red R	CSTSB4U/R	100	CSTSB5U/R	100
Blue BU	CSTSB4U/BU	100	CSTSB5U/BU	100
Black BL	CSTSB4U/BL	100	CSTSB5U/BL	100
Orange O	CSTSB4U/O	100	CSTSB5U/O	100
Green G	CSTSB4U/G	100	CSTSB5U/G	100
Yellow Y	CSTSB4U/Y	100	CSTSB5U/Y	100
White W	CSTSB4U/W	100	CSTSB5U/W	100

Accessories

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
End Plate	EPCSTSU	50	EPCSTSU	50
DIN Rail	2511120	20	2511120	20
32mm	CA701-15/S	20	CA701-15/S	20
35mm	2511160	10	2511160	10
End Stop	CA802	50	CA802	50
Insulated Jumper Fork Type	CA514/1-2	100	CA514/1-2	100
2 pole	CA514/1-3	50	CA514/1-3	50
3 pole	CA514/1-4	50	CA514/1-4	50
4 pole	CA514/3-2	100	CA514/3-2	100
Insulated Jumper Ring Lug	CA514/3-3	50	CA514/3-3	50
2 pole	CA514/3-4	50	CA514/3-4	50
3 pole	CSTSPC2	10	CSTSPC2	10
4 pole	CSTSPC2-1	10	CSTSPC2-1	10
Protective Cover	—	—	—	—
2 Terminal	CSTSPC1-2	10	CSTSPC1-2	10
3 Terminal	CSTSPC1-3	10	CSTSPC1-3	10
4 Terminal	CSTSPC1-4	10	CSTSPC1-4	10
100 mm				
200 mm				
300 mm				
Marking Tag	MT2B4	1 Pk. (100 tags)	MT2B4	1 Pk. (100 tags)

