

Coaxial Cable Connector 16_MMCX-50-1-2/111_O

Description

Right angle cable plug

Interface standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact crimped
Outer contact soldered
Weight 0.0009 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Brass	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing DOU-00006440
Catalogue drawing DOU-00006007
Assembly instruction DOC-0000179222

Ordering Information

Bulk 100 pcs package 16_MMCX-50-1-2/111_OH
Single package 16_MMCX-50-1-2/111_OE

Additional Information

Suitable cables K_01152-07