






RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS 1-6mm



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 2A 36 VDC
6. ELECTRIC LIFE: 200,000 CYCLES
7. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
8. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
9. OPERATING TEMP.: -20°C to 70°C
10. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 11. LAMP VOLTAGE: : RED 20mA 2.0V TYP., GREEN 20mA 3.1V TYP.
12. TRAVEL: 1.80mm
13. ACTUATION FORCE: 4.5 $\pm$ 1.5 N
14. MOUNTING NUT TORQUE: 1-3 Nm
15. INGRESS PROTECTION: IP67, IK10
16. HARDWARE SUPPLIED: O-RING AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-101692	print update	03/20/23	MW	TITLE SV4F23SS-3G1				100120873
					SCALE	DATE	DR	DWG	REV
					1:1	1/28/2022	MW	T840009	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED