






DESCRIPTION: RJ-45 TO 25-POSITION MALE D-SUB – PLASTIC & METALIZED PLASTIC

MATERIAL:

HOOD: ABS UL 94V-HB

RJADK25P70808Y1


SERIES _____
POSITIONS 25 _____
GENDER P = MALE _____
D-SUB TERMINALS 7 = CRIMP & POKE (CONTACTS PRE-CRIMPED) _____
MODULAR POSITIONS 08 _____
MODULAR POSITIONS LOADED 08 _____
COLOR _____
1 = BLACK
2 = METALIZED (SHIELD RATING: 60dB)
3 = GRAY
D-SUB CONTACT PLATING _____
1 = GOLD FLASH
3 = 10μ" DSUB CONTACT // 50μ" RJ-45 CONTACT



RJ45

- 1. BLUE
- 2. ORANGE
- 3. BLACK
- 4. RED
- 5. GREEN
- 6. YELLOW
- 7. BROWN
- 8. WHITE

DB-25M



FRONT VIEW

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH
DATE: 05/14/2007

UNITS = inch

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS

SHEET 1 OF 1

REV 2

DWG NO.

RJADK25P70808Y1