




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CHF2M**-X	.046 LB/10
1APHF2MWH-X	20.7 g/10

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. IS TO BE USED WITH THE MINI-COM BEZELS AND MINI-COM MODULES.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.



										MODEL FILENAME		SIZE			
										DRAWING FILENAME		A			
										D35544CC_DC27/00C					
										A 1/3 SIZE FLAT MODULE INSERT CUSTOMER DRAWING					
										PANDUIT® TINLEY PARK, IL 60487		I.I. NUMBER			
												PRODUCT SPEC/ PKG SPEC			
										THIRD ANGLE PROJECTION		ASSY METHOD/ TEST METHOD			
										ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.		SCALE			
										DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.3) (.XX) ±.03(.8) ANGLES ±		NONE			
26-6-11BJNJCOB. ADDED SUPPLEMEMNTAL P/N IAPHF2MWH-X35544-27JCOJCO										DRAWN BY RCA		REVIEW DRAWING NUMBERS		PART NO.	
19-11-97RCACEF A. REV'D DWG TITLE WAS 1/3-TWO POSITION FLAT INSERT.35544-27CEFC										DATE 1-17-97				SEE TABLE	
R1-17-97RCACEF RELEASED TO PRODUCTION35544-27CEF												MAT'L		DRAWING NO.	
REV DATE BY CHK DESCRIPTION ECN - R CUST SUP OTH										CHK'D CEFC		ABS		35544-27	