

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	8		0	RELEASED PER NPR 5705	24 APR 98	—	—
			A	ADDED −2 PER	17 SEP 98	PB	GS
				EC 0G1C−147−98			
				A1	REVISED PER ECO−09−020689		28AUG09



- 1 CABLE CLAMP WILL ACCEPT 34 WIRES OF 1.78 [.070] MAX DIA.
- 2 CABLE CLAMP WILL ACCEPT CABLE DIAMETERS BETWEEN 5.08−7.62 [.200−.300].
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

CABLE CLAMP
MATERIAL: CARBON STEEL
FINISH: 5.08μm [.000200] MIN NICKEL
2 EACH

4−40 UNC−2A FILLISTER HEAD SCREW
MATERIAL: CARBON STEEL
FINISH: ZINC
6 EACH

SHIELD
MATERIAL: CARBON STEEL
FINISH: 5.08μm [.000200] MIN NICKEL
2 EACH

AMP, PART NUMBER AND DATE CODE
IN THIS AREA



ASSEMBLED VIEW

3	OBSOLETE	2	213981−2
		1	213981−1
		NOTE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.DORWART	24 APR 98	AMP AMP Incorporated Harrisburg, PA 17105-3608	
		CHK M.McALONIS	27 APR 98		
DIMENSIONS: mm [INCHES]		APVD M.McALONIS	27 APR 98	NAME	
		PRODUCT SPEC		SHIELD KIT, UNASSEMBLED, 34 POSITION, M SERIES	
		-			
		APPLICATION SPEC			
		-			
MATERIAL		FINISH		SIZE	CAGE CODE
SEE CALLOUTS		SEE CALLOUTS		A2	00779
		WEIGHT		DRAWING NO	RESTRICTED TO
		-		C- 213981	-
		CUSTOMER DRAWING		SCALE	SHEET
				2:1	1 OF 1
				REV	A1