

Product data sheet

Characteristics

9001KYK14

30mm push button, Type K, control station, red momentary mushroom button, 6A inductive at 120VAC, STOP, NEMA 4, 13



Main

Range of Product	Harmony 9001K
Product or Component Type	Complete control station
Device short name	9001KY KY
Provided equipment	Contact block Legend plate
Contact block name	KA1

Complementary

Enclosure/cubicle description	Surface mounting
Enclosure material	Die cast zinc alloy Gray
Type of Installation	Indoor/outdoor
Control station composition	1 push-button 1 NO + 1 NC STOP
Connections - terminals	Screw-clamp terminals
[Ie] rated operational current AC	10 A

Environment

NEMA degree of protection	NEMA 3/4/13
---------------------------	-------------

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901513384
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.70 in (32.258 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	32.26 in (81.935 cm)
Package 1 Weight	3.06 lb(US) (1.388 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------