

6

5

4

3



2

1


APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	9/9/20	



WITH LC DUST CAP



43.85±0.50




19.85±0.25

4.00±0.15

2-Ø3.10±0.15

9.80±0.15



SHRAPNEL (SEE TABLE)

20.00±0.25

25.00±0.25

OPMF1ANNC1NC	PEI RED	W/O SHRAPNEL
OPMF1ANNC1PC	PEI RED	W/SHRAPNEL
OPMD1ANNC1NC	PEI Water blue	W/O SHRAPNEL
OPMD1ANNC1PC	PEI Water blue	W/SHRAPNEL
OPMB1ANNC1NC	PEI Blue	W/O SHRAPNEL
OPMB1ANNC1PC	PEI Blue	W/SHRAPNEL
OPMA1ANNC1NC	PEI Green	W/O SHRAPNEL
OPMA1ANNC1PC	PEI Green	W/SHRAPNEL
Part name	Material, Color	SHRAPNEL

SPECIFICATIONS:

Material:

Housing: PEI, rated UL 94V-0, Color: See Chart

Electrical:

Standards of IEC,EIA/TIA, Telcordia

Repeatability: 500 cycles min

Insertion loss: 0.2dB max

Temperature Rating:

Operating temperature: -40°C to +75°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

MM	ANGLE
X. ± 0.35	X.° ± 2°
.X ± 0.30	.X° ± 1°
.XX ± 0.25	.XX° ± 0.5°
.XXX ± 0.15	.XXX° ± 0.5°

APPROVALS		DATE
DRAWN	LH	9/9/20
CHECKED	JL	9/9/20
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
OPTICAL MPO ADAPTERS, 1 PORTS, LONG-EARED,
WITH MPO DUST CAP

SIZE	PART NO.	REV.
X	OPMX1ANNC1XC	-
REF: S00005C	SCALE: NTS	SHEET 1 OF 1