



- NOTES:
1. PARTS TO BE BULK PACKED.
2. SOLDER CONTACTS ARE PRESSED INTO CONNECTOR.
SIZE 12 CONTACTS AND SIZE 26 (POSITIONS 3, 7 & 8) FACE TOP KEY (UP).
SIZE 26 CONTACTS (POSITIONS 4-6) FACE DOWN.
3. ALL DIMENSIONS ARE FOR REFERENCE ONLY EXCEPT WHERE NOTED WITH TOLERANCE.


ASSY P/N	COUPLING RING P/N	CABLE O.D.
W3B82-8PG-335	4282V4	.350-.370 IN. [8.9-9.4mm]
W3B82-8PG-335W	4482V4	.350-.370 IN. [8.9-9.4mm]



STD COUPLING RING
P/N: W3B82-8PG-3XX



WINGED COUPLING RING
P/N: W3B82-8PG-3XXW



A	AB	05-09-19	RELEASE PER DOR 14-6281TC
REV.	INIT.	DATE	DESCRIPTION
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.		ORIG. DRAWN BY: AB	DATE: 07-21-14
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.		CHECKED BY:	
		APPROVED BY:	
SCALE	SIZE	SHEET	conxall 601 E. WILDWOOD VILLA PARK, IL 60181
NTS	B	1 OF 1	
FILE:	DIRECTORY:	PART NUMBER:	TITLE: CABLE END CONNECTOR KIT (2)#12 + (6)#26 PIN CONTACTS, SOLDER CUP MULTI-CON-X, WEATHER RESISTANT STANDARD PRODUCT
= CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX		SLW	CUSTOMER: STANDARD PRODUCT
W3B82-8PG-3XX(W)			REV A