


4

3

2

1



4

3



2

1


THIS DRAWING IS UNPUBLISHED.  
RELEASED FOR PUBLICATION MAY 1990 .  
© COPYRIGHT 1990 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC |  | DIST |     | REVISIONS   |             |      |     |
|-----|--|------|-----|-------------|-------------|------|-----|
| J   |  |      |     | 変更          | DESCRIPTION | DATE | DWN |
|     |  | P    | LTR | SEE SHEET 1 |             |      |     |
|     |  |      |     |             |             |      |     |
|     |  |      |     |             |             |      |     |
|     |  |      |     |             |             |      |     |
|     |  |      |     |             |             |      |     |
|     |  |      |     |             |             |      |     |
|     |  |      |     |             |             |      |     |
|     |  |      |     |             |             |      |     |

-1 ; AS SHOWN  
本図



パネル取付寸法  
PANEL CUT OUT DIMENSION



B-B  
(SCALE 2:1)

|                                        |  |                  |  |                    |  |                              |  |
|----------------------------------------|--|------------------|--|--------------------|--|------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN              |  | <b>tyco</b>        |  | Tyco Electronics AMP K.K.    |  |
|                                        |  | CHK              |  | <b>Electronics</b> |  | Kawasaki, Japan              |  |
|                                        |  | APVD             |  | NAME               |  | アンブ ラティス コネクター               |  |
|                                        |  | PRODUCT SPEC     |  | 製品規格               |  | 12極 嵌合状態参考図                  |  |
|                                        |  | APPLICATION SPEC |  | 取付適用規格             |  | AMP LATTICE CONNECTOR 12POS. |  |
|                                        |  | WEIGHT           |  | SIZE               |  | CAGE CODE                    |  |
|                                        |  |                  |  | A3                 |  | 00779                        |  |
|                                        |  |                  |  | DRAWING NO         |  | 番号                           |  |
|                                        |  |                  |  | C-176764           |  | RESTRICTED TO                |  |
|                                        |  |                  |  | SCALE              |  | SHEET                        |  |
|                                        |  |                  |  | 1:1                |  | 2 OF 8                       |  |
|                                        |  |                  |  | REV                |  | D                            |  |



4

3




2


1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION MAY 1990 .  
© COPYRIGHT 1990 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC |  | DIST |     | REVISIONS |             |  |  | DATE | DWN | APVD |
|-----|--|------|-----|-----------|-------------|--|--|------|-----|------|
| J   |  | P    | LTR | 変更        | DESCRIPTION |  |  |      |     |      |
|     |  |      |     |           | SEE SHEET 1 |  |  |      |     |      |

-2 ; AS SHOWN  
本図



|                                                                                       |  |                                                                 |     |                      |                                        |                            |                           |                                                             |  |                  |  |               |  |       |  |
|---------------------------------------------------------------------------------------|--|-----------------------------------------------------------------|-----|----------------------|----------------------------------------|----------------------------|---------------------------|-------------------------------------------------------------|--|------------------|--|---------------|--|-------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  |                                                                 | DWN |                      | <div>tyco</div> <div>Electronics</div> |                            | Tyco Electronics AMP K.K. |                                                             |  |                  |  |               |  |       |  |
|                                                                                       |  |                                                                 | CHK |                      |                                        |                            | Kawasaki,Japan            |                                                             |  |                  |  |               |  |       |  |
| DIMENSIONS:<br>単位： 耗<br>MM                                                            |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>一般公差               |     | APVD                 |                                        | NAME<br>名称                 |                           | アンプ ラティス コネクター<br>12極 嵌合状態図<br>AMP LATTICE CONNECTOR 12POS. |  |                  |  |               |  |       |  |
|  |  | 0 PLC ±<br>1 PLC ±<br>2 PLC ±<br>3 PLC ±<br>4 PLC ±<br>ANGLES ± |     | PRODUCT SPEC<br>製品規格 |                                        | APPLICATION SPEC<br>取付適用規格 |                           |                                                             |  |                  |  |               |  |       |  |
|                                                                                       |  | 3                                                               |     | —                    |                                        | —                          |                           |                                                             |  |                  |  |               |  |       |  |
| MATERIAL<br>材料                                                                        |  | FINISH<br>仕上                                                    |     | WEIGHT               |                                        | SIZE                       |                           | CAGE CODE                                                   |  | DRAWING NO<br>番号 |  | RESTRICTED TO |  |       |  |
|                                                                                       |  |                                                                 |     | —                    |                                        | A3                         |                           | 00779                                                       |  | C-176764         |  | —             |  |       |  |
| CUSTOMER DRAWING                                                                      |  |                                                                 |     |                      |                                        |                            |                           |                                                             |  | SCALE<br>尺度 1:1  |  | SHEET 4 OF 8  |  | REV D |  |

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

MAY 1990 .

© COPYRIGHT 1990 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC  
JDIST  
P LTR

REVISIONS

変更



DESCRIPTION

DATE

DWN




APVD

SEE SHEET 1




-3 ; AS SHOWN  
本図

A-A

NOT SECTIONED



(SCALE 2:1)



- 1 APPLICABLE SPECIFICATIONS  
 PRODUCT SPEC. : 108-5315  
 APPLICATION SPEC. : 114-5147  
 2 INSTRUCTION SHEET : 411-5507  
 3 GENERAL TOLERANCE  
 0 < \* ≤ 10 : ±0.2  
 10 < \* ≤ 30 : ±0.25  
 30 < \* ≤ 100 : ±0.3  
 ANGLES : ±3°

- 1 適用規格  
 製品規格 : 108-5315  
 取付適用規格 : 114-5147  
 2 取扱説明書 : 411-5507  
 3 一般公差  
 0 < \* ≤ 10 : ±0.2  
 10 < \* ≤ 30 : ±0.25  
 30 < \* ≤ 100 : ±0.3  
 ANGLES : ±3°

|     |                                                                            |                                                            |           |             |
|-----|----------------------------------------------------------------------------|------------------------------------------------------------|-----------|-------------|
| 2   | STEEL, NICKEL PLATED<br>スチール、ニッケルめっき                                       | TAP-TIGHT B-TIGHT M2.6 SCREW<br>M2.6 タップタイト Bタイト           | 900035-1  | ⑤           |
| 2   | STEEL, NICKEL PLATED<br>スチール、ニッケルめっき                                       | TAP-TIGHT P-TIGHT M3<br>M3 タップタイト Pタイト                     | 900034-1  | ④           |
| 1   | STEEL, NICKEL PLATED<br>スチール、ニッケルめっき                                       | CLAMP<br>クランプ                                              | 176832-1  | ③           |
| 1   | THERMAL PLASTIC(94-HB), COLOR; ART GRAY 5.5<br>熱可塑性樹脂(94-HB), 色;アートグレイ 5.5 | R/A COVER "B" 12POS.<br>ライトアングル カバー"B" 12極                 | 177658-1  | ②           |
| 1   | THERMAL PLASTIC(94-HB), COLOR; ART GRAY 5.5<br>熱可塑性樹脂(94-HB), 色;アートグレイ 5.5 | R/A COVER "A" WITH LOCK 12POS.<br>ライトアングル カバー"A" ロック付き 12極 | 177659-1  | ①           |
| QTY | 材料及び仕上<br>MATERIAL & FINISH                                                | 名称<br>NAME                                                 | 型番<br>P/N | ITEM<br>NO. |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

製品規格

APPLICATION SPEC

取付適用規格

WEIGHT

CUSTOMER DRAWING

tyco  
ElectronicsTyco Electronics AMP K.K.  
Kawasaki, Japan

NAME

名称

アンプ ラティス コネクター  
 ライトアングル ケーブルクランプ キット 12極  
 AMP LATTICE CONN.  
 R/A CABLE CLAMP KIT 12POS.

SIZE

CAGE CODE

DRAWING NO

番号

A3

00779

C-

176764

RESTRICTED TO

SCALE  
尺度 1:1SHEET  
5 OF 8REV  
D

4

3




2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION MAY 1990 .  
© COPYRIGHT 1990 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC |  | DIST |     | REVISIONS |             |  |  | DATE | DWN | APVD |
|-----|--|------|-----|-----------|-------------|--|--|------|-----|------|
| J   |  | P    | LTR | 変更        | DESCRIPTION |  |  |      |     |      |
|     |  |      |     |           | SEE SHEET 1 |  |  |      |     |      |

-3 ; AS SHOWN  
本図



|                                                                           |  |  |  |                            |  |                                                                             |  |               |  |
|---------------------------------------------------------------------------|--|--|--|----------------------------|--|-----------------------------------------------------------------------------|--|---------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                    |  |  |  | DWN                        |  | <b>tyco</b> Tyco Electronics AMP K.K.<br><b>Electronics</b> Kawasaki, Japan |  |               |  |
| DIMENSIONS:<br>単位: 概<br>MM                                                |  |  |  | CHK                        |  | NAME<br>名称                                                                  |  |               |  |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>一般公差                         |  |  |  | APVD                       |  | アンブ ラティス コネクター<br>12極 嵌合状態図<br>AMP LATTICE CONN. 12P, R/A TYPE.             |  |               |  |
| 0 PLC ± 3<br>1 PLC ± 3<br>2 PLC ± 3<br>3 PLC ± 3<br>4 PLC ± 3<br>ANGLES ± |  |  |  | PRODUCT SPEC<br>製品規格       |  | SIZE                                                                        |  | CAGE CODE     |  |
| MATERIAL<br>材料                                                            |  |  |  | APPLICATION SPEC<br>取付適用規格 |  | DRAWING NO<br>番号                                                            |  | RESTRICTED TO |  |
| FINISH<br>仕上                                                              |  |  |  | WEIGHT                     |  | A3                                                                          |  | 00779         |  |
|                                                                           |  |  |  | CUSTOMER DRAWING           |  | SCALE<br>尺度                                                                 |  | 1:1           |  |
|                                                                           |  |  |  |                            |  | SHEET                                                                       |  | 6 OF 8        |  |
|                                                                           |  |  |  |                            |  | REV                                                                         |  | D             |  |

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

MAY 1990.

© COPYRIGHT 1990 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

DESCRIPTION

DATE




DWN

APVD


SEE SHEET 1

-4 ; AS SHOWN




本図



A-A



(SCALE 2:1)



## 1 APPLICABLE SPECIFICATIONS

PRODUCT SPEC. : 108-5315

APPLICATION SPEC. : 114-5147

## 2 INSTRUCTION SHEET : 411-5507

## △ GENERAL TOLERANCE

0 &lt; \* ≤ 10 : ±0.2

10 &lt; \* ≤ 30 : ±0.25

30 &lt; \* ≤ 100 : ±0.3

ANGLES : ±3°

## 1 適用規格

製品規格 : 108-5315

取付適用規格 : 114-5147

## 2 取扱説明書 : 411-5507

## △ 一般公差

0 &lt; \* ≤ 10 : ±0.2

10 &lt; \* ≤ 30 : ±0.25

30 &lt; \* ≤ 100 : ±0.3

ANGLES : ±3°


|     |                                                                            |                                                                   |           |             |
|-----|----------------------------------------------------------------------------|-------------------------------------------------------------------|-----------|-------------|
| 2   | STEEL, NICKEL PLATED<br>スチール、ニッケルめっき                                       | TAP-TIGHT B-TIGHT M2.6 SCREW<br>M2.6 タップタイト Bタイト                  | 900035-1  | ⑤           |
| 2   | STEEL, NICKEL PLATED<br>スチール、ニッケルめっき                                       | TAP-TIGHT P-TIGHT M3<br>M3 タップタイト Pタイト                            | 900034-1  | ④           |
| 1   | STEEL, NICKEL PLATED<br>スチール、ニッケルめっき                                       | CLAMP<br>クランプ                                                     | 176832-1  | ③           |
| 1   | THERMAL PLASTIC(94-HB), COLOR; ART GRAY 5.5<br>熱可塑性樹脂(94-HB), 色;アートグレイ 5.5 | R/A COVER "B" 12POS.(Ø10.5)<br>ライトアングル カバー"B" 12極                 | 177658-2  | ②           |
| 1   | THERMAL PLASTIC(94-HB), COLOR; ART GRAY 5.5<br>熱可塑性樹脂(94-HB), 色;アートグレイ 5.5 | R/A COVER "A" WITH LOCK 12POS.(Ø10.5)<br>ライトアングル カバー"A" ロック付き 12極 | 177659-2  | ①           |
| QTY | 材料及び仕上<br>MATERIAL & FINISH                                                | 名称<br>NAME                                                        | 型番<br>P/N | ITEM<br>NO. |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

DIMENSIONS:  
単位: 概  
MMTOLERANCES UNLESS  
OTHERWISE SPECIFIED:  
一般公差

|        |   |
|--------|---|
| 0 PLC  | ± |
| 1 PLC  | ± |
| 2 PLC  | ± |
| 3 PLC  | ± |
| 4 PLC  | ± |
| ANGLES | ± |

MATERIAL  
材料SEE TABLE  
表参照FINISH  
仕上SEE TABLE  
表参照

WEIGHT

CUSTOMER DRAWING

tyco  
ElectronicsTyco Electronics AMP K.K.  
Kawasaki, JapanNAME  
名称アンプ ラティス コネクター (Ø10.5)  
ライトアングル ケーブルクランプ キット 12極

AMP LATTICE CONN.

R/A CABLE CLAMP KIT 12POS.

SIZE

CAGE CODE

DRAWING NO

A3 00779

C-176764

RESTRICTED TO

SCALE  
尺度 1:1SHEET  
7 OF 8REV  
D

4

3



2

1


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION MAY 1990 .  
© COPYRIGHT 1990 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC |  | DIST |     | REVISIONS |             |  |  | DATE | DWN | APVD |
|-----|--|------|-----|-----------|-------------|--|--|------|-----|------|
| J   |  | P    | LTR | 変更        | DESCRIPTION |  |  |      |     |      |
|     |  |      |     |           | SEE SHEET 1 |  |  |      |     |      |

-4 ; AS SHOWN  
本図



B-B  
(SCALE 2:1)



|                                                   |  |                            |  |                                          |  |                             |  |
|---------------------------------------------------|--|----------------------------|--|------------------------------------------|--|-----------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.            |  | DWN                        |  | tyco                                     |  | Tyco Electronics AMP K.K.   |  |
| DIMENSIONS:<br>単位: 概<br>MM                        |  | CHK                        |  | Electronics                              |  | Kawasaki, Japan             |  |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>一般公差 |  | APVD                       |  | NAME<br>名称                               |  | アンプ ラティス コネクター<br>12極 嵌合状態図 |  |
| 0 PLC ± 3                                         |  | PRODUCT SPEC<br>製品規格       |  | AMP LATTICE CONN. 12P, R/A TYPE. (Ø10.5) |  | SIZE                        |  |
| 1 PLC ±                                           |  | APPLICATION SPEC<br>取付適用規格 |  | CAGE CODE                                |  | DRAWING NO                  |  |
| 2 PLC ±                                           |  | WEIGHT                     |  | A3                                       |  | 00779                       |  |
| 3 PLC ±                                           |  | CUSTOMER DRAWING           |  | SCALE                                    |  | SHEET                       |  |
| 4 PLC ±                                           |  | FINISH<br>仕上               |  | 1:1                                      |  | 8 OF 8                      |  |
| MATERIAL<br>材料                                    |  | RESTRICTED TO              |  | REV                                      |  | D                           |  |