





DIALIGHT PART NUMBER	NUMBER OF POSITIONS	DIMENSION "A" (BAR LENGTH) METRIC, [INCHES]	OPERATING CHARACTERISTICS @ T _A = 25°C								
			COLOR	VIEWING ANGLE	FORWARD VOLTAGE (V)		REVERSE VOLTAGE	PEAK WAVELENGTH (nm)	LUMINOUS INTENSITY (mcd)		TEST CONDITIONS
					TYP	MAX		TYP	MIN	TYP	
HLMP-1300-102	2	8.76-9.65, [.346-.380]	RED	60°	1.9	2.4	5 V @ I _R = 100 μA	635	8.6	13.8	I _F = 10 mA
HLMP-1300-103	3	13.36-14.22, [.526-.560]									
HLMP-1300-104	4	18.54-19.02, [.730-.749]									
HLMP-1301-102	2	8.76-9.65, [.346-.380]									
HLMP-1301-103	3	13.36-14.22, [.526-.560]									
HLMP-1301-104	4	18.54-19.02, [.730-.749]									
HLMP-1301-106	6	27.94-28.45, [1.100-1.120]									
HLMP-1301-108	8	37.39-37.72, [1.472-1.485]									
HLMP-1302-102	2	8.76-9.65, [.346-.380]		45°	2.2	3.0		8.6	12.0		
HLMP-1302-104	4	18.54-19.02, [.730-.749]									
HLMP-1302-107	7	32.64-33.15, [1.285-1.305]									
HLMP-1321-104	4	18.54-19.02, [.730-.749]									
HLMP-1340-104	4	18.54-19.02, [.730-.749]									
HLMP-1385-108	8	37.39-37.72, [1.472-1.485]									
			60°	2.2	3.0			6.0	10.0	I _F = 10 mA	

MAXIMUM RATINGS				
	HLMP-1300-1XX, HLMP-1301-1XX, HLMP-1302-1XX	HLMP-1321-104	HLMP-1340-104	HLMP-1385-108
LINEAR DERATION FROM 25°C	—	1.8 mW/°C	—	1.8 mW/°C
LINEAR DERATION FROM 50°C	0.5 mA/°C	—	—	—
D.C. FORWARD CURRENT	30 mA			
OPERATING TEMPERATURE	-55°C TO 100°C			
STORAGE TEMPERATURE	-55°C TO 100°C			
LEAD SOLDERING TEMPERATURE	260°C FOR 5 SEC			



DIMENSIONS:
mm
[inches]



SCALE 2.000

REV.	ECN NO.	REVISIONS	DRN.	CKD.	APP.	DATE
A	—	NEW RELEASE	M.C.	D.C.	N.O.	3-12-99
B	—	REVISED ELECTRO/OPTICAL SPECS. AND 90° ±5° WAS 90° ±10°.	M.C.			

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.			DRAWING NUMBER		REV
SCALE 4:1			C-16497		B
ALL DIM'S IN: INCHES			TITLE		
TOLERANCES: UNLESS OTHERWISE SPECIFIED			Ø 3.00 mm CBI ARRAY, RED		
FRACTIONS: ±1/64			MATERIAL		
DECIMALS (.XX): ±.01					
DECIMALS (.XXX): ±.005					
DECIMALS (.XXXX): ±.0005					
ANGLES: ±1°					
FINISH:					
FSCM 83330					
			Dialight		1913 ATLANTIC AVE. MANASQUAN, N.J. 08736
			SHEET OF		FAMILY TABLES: