

## M23 Metal Screw Cover – no Chain



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 100 9101
Specification	M23 Metal Screw Cover – no Chain
HARTING eCatalogue	<a href="https://b2b.harting.com/09151009101">https://b2b.harting.com/09151009101</a>

### Identification

Category	Hoods/Housings
Series	Circular connectors M23
Identification	Signal
Type of hood/housing	Cover
Description of hood/housing	for cable to cable housing

### Version

Size	M23
Locking type	Screw locking

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 locked condition IP69 / IPX9K acc. to ISO 20653 locked condition

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

## Commercial data

Packaging size	5
Net weight	12.3 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140184220
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors