

Coaxial Cable Connector 11_N-75-4-9/133_N

Description

Straight cable plug

Interface standards

IEC 60169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	75 Ω
Interface frequency max.	1.5 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0287 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPALATE (R) Plating
Body	Brass	SUCOPALATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPALATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPALATE (R) Plating

Related Documents

Catalogue drawing	DOU-00006925
Assembly instruction	DOC-0000179851

Ordering Information

Single package	11_N-75-4-9/133_NE
----------------	--------------------

Additional Information

Suitable cables	G_04233_D, G_04233_D-01
-----------------	-------------------------