





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		C1	REVISED PER ECR-06-026732	17NOV06	HMR	GJ

- 1 SPECIFICATIONS:
MAGNET WIRE #18 - #34 AWG, .040"(1.02mm)-
.006"(0.16mm) DIA COPPER. OTHER SIZES MAY BE
ACCOMMODATED, CONSULT TYCO ELECTRONICS FOR APPROVAL.
- 2 POCKET RECOMMENDATION: #1601425
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS
SPECIFICATION 114-13166 FIGURE 6
- 4 ENTIRE TERMINAL IS POST PLATED WITH .000050[1.27 MICRONS]
MIN NICKEL. AREA INDICATED ALSO PLATED WITH
.000050[1.25 MICRONS] MIN GOLD.
- 5 PRELIMINARY - NOT FOR PRODUCTION



NON-STANDARD	4	5	3-1601174-3
NON-STANDARD	PRE-TIN PLATE		3-1601174-2
STANDARD	PRE-TIN PLATE		1601174-2
-	-		-
PACKAGING	FINISH	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	27JAN2003	tyco Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK	27JAN2003				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ± -		PRODUCT SPEC			
		1 PLC ± -		108-2085			
MATERIAL		2 PLC ± .01[0.25]		APPLICATION SPEC			
		3 PLC ± .005[0.13]		3			
BRASS, 1/2 HARD		FINISH		WEIGHT	-	SIZE	A2
SEE TABLE		CUSTOMER DRAWING		DRAWING NO		CAGE CODE	00779
				C=1601174		RESTRICTED TO	-
				SCALE	6:1	SHEET	1 of 1
						REV	C1