

Coaxial Cable Connector 21_PC35-50-3-3/199_U

Description

Straight cable jack

Interface standards

IEC 60169-23

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	26.5 GHz

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.00478 kg

Environmental Data

Operating temperature	-60 °C to 100 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PS (Polystyrene)	

Related Documents

Outline drawing	DOU-00064414
Catalogue drawing	DCA-00089662
Assembly instruction	DOC-0000215467

Ordering Information

Single package	21_PC35-50-3-3/199_UE
----------------	-----------------------

Additional Information

Suitable cables	EZ_141_TP_M17, EZ_141_AL_TP_M17, SUCOFORM_141, MULTIFLEX_141
-----------------	--