

Han PushPull Power metal base panel



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 002 0303
Specification	Han PushPull Power metal base panel
HARTING eCatalogue	https://b2b.harting.com/09350020303

Identification

Category	Connectors
Series	Han® PushPull (V14)
Type of hood/housing	Bulkhead mounted housing

Version

Locking type	PushPull
--------------	----------

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene

Specifications and approvals

Specifications	IEC 61076-3-117
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	12.68 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140053595
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors