

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010505](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Adapter for RJ45 Patch Cord](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	«23x13»
Component Type	RJ45 Adapter
Insert Series	S-M/RJ45
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	EN 50173-1, EN 60664-1, EN 61984, ISO/IEC 11801
UPC	887191825274
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Insert Color	Grey
Material - Insert	Polycarbonate
Net Weight	3.800/g
Number of Rows	1
Packaging Type	Bag
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +85°C
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	50V
Material Info	
Engineering Number	7701.3566.0



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Contained

Search Parts in this Series
[93601](#) Series

Mates With
[936010503](#) Gender Changer, [936010504](#)
RJ45 Male Insert

Use With
RJ45 Patch Cords

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION