

RAFIX 16 F - Blanking cap, black**5.05.800.063/0000****General information**

Form of lens	flat lens
Color of lens	opaque black
Form of collar	square

Dimensions

Installation dimensions	23,1 x 23,1 mm
Dimenions	24,9 x24,9
Length of collar	24.9 mm
Key grid	25 x 25 mm
Width of collar	24.9 mm
Overall height	1.7 mm
Mounting depth	26.2 mm
Mounting hole	23.1 x 23.1 mm

Mechanical design

Mounting	ring nut
Illumination	no

Mechanical characteristics

Robustness min.	100 N
-----------------	-------

Electrical characteristics

Protection class	II
------------------	----

Other specifications

Color	black
Operating life (operations)	2,000,000 momentary / 100,000 latching cycle
Degree of protection from front side	IP65 (DIN EN 60529)
Ambient temp. operating min.	-25 °C
Ambient temp. operating max. without lamp / LED	+70 °C
Ambient temp. operating max. with lamp /LED	+55 °C
Storage temperature min.	-40 °C
Storage temperature max.	+85 °C
Environmental restistance	acc. to IEC 60068-2-14, -30, -33 and -78
ROHS compliant	yes
REACH compliant	yes

Panel cut-out

