

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731120430](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT Stamped Contact, Male, Crimp, 0.10µm Gold Plating, 20-24 AWG

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	D-Sub Products
Series	173112
Comments	Packaging Detail: 10 strips of 25 pieces in a box
Contact Type	Stamped Crimp
Overview	FCT D-Sub Connectors
Product Category	Contacts
Product Name	FCT Products
Type	Standard Density
UPC	191128225908
Physical	
Durability (mating cycles max)	50
Gender	Male
Material - Contact	Copper Alloy
Net Weight	0.100/g
Orientation	Straight
Packaging Type	Carton
Plating - Contact	Gold over Nickel
Plating min - Mating	0.100µm
Temperature Range - Operating	-55° to +125°C
Termination Style	Crimp
Wire Size AWG	20, 22, 24
Electrical	
Current - Maximum per Contact	5.0A
Material Info	
Engineering Number	P7L



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Not Reviewed For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
Green Image Not Relevant Not Contained	

Search Parts in this Series
[173112](#) Series

Use With
FCT Standard-Density Connectors

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION